



HILCO ZILVERSOLDEERSTAVEN

Autogeenlasstaven - non-ferro - zilver solderen

Zilver-koper-fosforhardsoldeerstaven							
Type	Samenstelling				Smelttraject	Classificatie	
	Ag	Cu	P	Overig		AWS A5.8	ISO 17672
L-Ag 2 P	2,0	91,8	6,2	-	645 - 825 °C	~BCuP-6	CuP 279
L-Ag 5 P	5,0	89,0	6,0	-	645 - 815 °C	BCuP-3	CuP 281 ^a
L-Ag 15 P	15,0	80,0	5,0	-	645 - 800 °C	BCuP-5	CuP 284

Cadmiumvrije zilver soldeerstaven							
Type	Samenstelling				Smelttraject	Classificatie	
	Ag	Cu	Zn	Overig		AWS A5.8	ISO 17672
L-Ag 20 Si¹	20,0	43,9	Bal.	Si: 0,1	690 - 810 °C	-	Ag 220
L-Ag 30 Sn	30,0	36,0	Bal.	Sn: 2,0	665 - 755 °C	-	Ag 130
L-Ag 34 Sn¹	34,0	36,0	Bal.	Sn: 3,0	630 - 730 °C	~BAg-35	Ag 134
L-Ag 45 Sn¹	45,0	27,0	Bal.	Sn: 3,0	640 - 660 °C	BAg-36	Ag 145
L-Ag 55 Sn¹	55,0	21,0	Bal.	Sn: 3,0	630 - 660 °C	~BAg-7	Ag 155

Opmerking:

¹ deze zilver soldeerstaven zijn ook verkrijgbaar als flux beklede staven (FC)